



## SIGNAL REFERENCE GRID WIRE CLAMP, #8 STRANDED-#4 STRANDED

### CATALOG NUMBER

---

**RGC**



### FEATURES

---

Provides a quick method to support a signal grid to computer floor pedestals

Slots in fastener grip wire to provide positive contact with post

Clamps grid wire directly to post allowing a low resistance connection across bare metal contacts

Installs easily with a screwdriver or nut driver

### PRODUCT ATTRIBUTES

---

Material: Steel

Finish: Electrogalvanized

Conductor Size: #8 Stranded - #4 Stranded

Diameter 1: 3/4" – 1"

Diameter 2: 0.146" – 0.280"

### ADDITIONAL PRODUCT DETAILS

---

RGC can be installed on 3/4" to 1" round or square pedestals.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**nVent.com** CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.