

# BOLT CLOSE CONDUIT/PIPE CLAMP, STEEL, 1" EMT, 1" RIGID/PIPE, 1/4" HOLE

# **CATALOG NUMBER**

CD2B



## CERTIFICATIONS




# **FEATURES**

Retained bolt and built-in nut means there are less parts to handle or drop

Combo head bolt works with slotted, hex, #3 phillips or #2 robertson drivers

| RODUCT ATTRIBUTES               |
|---------------------------------|
| Material: Steel                 |
| Finish: Electrogalvanized       |
| Nut Type: Built-In Nut          |
| Duter Diameter: 1.000" – 1.315" |
| EMT Conduit Size: 1"            |
| Rigid Conduit/Pipe Size: 1"     |
| Hole Size: 1/4"                 |
| Static Load 1: 200 lb           |

# DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

### APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of

their respective owners. nVent reserves the right to change specifications without notice.