



LED Highbay

75HB/LED/850/ND FB 4/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	75-175W
Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	240 °
Luminous Flux (Nom)	8500 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	113.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	75 W
Lamp Current (Nom)	650 mA
Wattage Equivalent	175 W


Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	98 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T-shape
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	75HB/LED/850/ND FB 4/1
EAN/UPC - Product	046677542313
Order code	929001990504

LED Highbay

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001990504

Net Weight (Piece)	0.648 kg
--------------------	----------



Dimensional drawing



75HB/LED/850/ND FB 4/1


Product	D	C
75HB/LED/850/ND FB 4/1	141 mm	267 mm

Photometric data



LEDTrueForce HB EX39 200D 75 850



LEDTrueForce HB EX39 200D 75 850



LEDTrueForce HB EX39 200D 75

LED Highbay

Lifetime



LEDTrueForce HB EX39 200D

LEDTrueForce HB EX39 200D

