



LED Highbay

38HB/LED/840/ND FB 6/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Product data

General information	
Cap-Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	38-85W

Light technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	200 °
Luminous Flux (Nom)	3800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	38 W
Lamp Current (Nom)	320 mA
Wattage Equivalent	85 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.92
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and dimming	
Dimmable	No

Mechanical and housing	
Bulb Finish	Frosted
Bulb Shape	T-shape

Approval and application	
Energy Consumption kWh/1000 h	- kWh


Product data	
Order product name	38HB/LED/840/ND FB 6/1
EAN/UPC - Product	046677543075
Order code	929001999204

LED Highbay

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001999204

Net Weight (Piece)	0.247 kg
--------------------	----------


Dimensional drawing




38HB/LED/840/ND FB 6/1

Product	D	C
38HB/LED/840/ND FB 6/1	138 mm	238 mm


Photometric data



LEDTrueForce E26 120-240V 38HB




LEDTrueForce E26 120-240V 38HB 840 42W




LEDTrueForce E26 120-240V 38HB 840 42W

Lifetime



LEDTrueForce E26 120-240V



LEDTrueForce E26 120-240V

