oject:		Туре:		Date:		Notes:	
--------	--	-------	--	-------	--	--------	--



Р





IDEAL APPLICATIONS



DESCRIPTION:

The WL-LED26 is a compact, energy efficient wall light is a great security lighting option for building entrances, loading areas, walkways, and exit doors.

FEATURES:

- Sturdy construction with durable aluminum housing and clear polycarbonate lens to withstand harsh weather conditions.
- The fixture has a 1/2" NPT conduit entry at the bottom and a 1/2" knockout in the back for conduit entry.
- Mounts to a standard junction box.
- Clear polycarbonate lens and white reflector creates bright, widespread illumination.
- Electronic photocell included for dusk to dawn operation.
- Ideal for mounting heights of 10' 20'.
- Replaces 70W Metal Halide fixtures.

SPECIFICATIONS	WL-LED26
Watts	26.19W
Lumens	3,258 Lm
Efficacy	124 Lm/W
Replaces	70W MH
Voltage	120-277V
Colour Temp	5000K
CRI	74.5
Dimming	0-10V Dimming
THD	14.1%
PF	0.99
LED Life (L80)	>54,000 hours
Operating Temp	-40°C to +40°C
Housing Material	Die Cast Aluminum
Mounting	Wall Mount
Accessories Sold Separately	Wire cage
Certification	ETL Listed, 5 Year Warranty, Wet Locations, DLC Standard













DIMENSIONS:




ACCESSORIES (WIRE CAGE ORDER SEPARATELY):






WL-LED26-B-5K-DIM-PC-CL MOUNTED AT 10FEET





ORDERING GUIDE:



Note: Photocell can be deactivated by disconnecting the wires to the photocell.

(Remove the threaded button photocell $\,$ and disconnect wires, ensure to fasten the photocell for proper sealing).

ORDERING GUIDE

Check the items that you wish to order:	
093454 WL-LED26-B-5K-BRZ-DIM-PC-CL 098016 - WIRE CAGE ZINC PLATED STEEL F/WL	