



# Hybrid Pliers with Crimper, Fish Tape Puller and Wire Stripper



Pliers strip, cut, pull, twist, shear and crimp with one tool. These hybrid pliers feature a built-in channel to pull steel fish tape without damaging the wire. With full length, induction hardened knives and a high-leverage design, these hybrid pliers provide more cutting power on hard wire. It easily strips 10-14 AWG solid and 12-16 stranded wire. The wide, knurled head easily grabs and twists wires. Convenient holes for shearing 6-32 and 8-32 bolts plus a crimper for non-insulated connectors, lugs and terminals make this a must-have tool for your bag.

## Specifications

<b>Type:</b>	High Leverage Stripping Crimping Shearing Side-Cut Hybrid Plier	<b>Application:</b>	Strip (10-14 SLD)(12-16 STR), Bolt Shear #6-32 and #8-32, Crimps Non-Insulated Connectors, Lugs and Terminals, Cuts Screws, Nails and Most Hardened Wire
<b>Special Features:</b>	High-Leverage Design	<b>Overall Length:</b>	8.981" (22.8 cm)
<b>Overall Height:</b>	0.75" (2 cm)	<b>Overall Width:</b>	2.25" (6 cm)
<b>Material:</b>	Chrome-Vanadium Steel	<b>Nose Type:</b>	Square
<b>Jaw Length:</b>	2.04" (0 cm)	<b>Jaw Width:</b>	1.154" (0 cm)
<b>Jaw Thickness:</b>	0.6" (1.5 cm)	<b>Jaw Capacity:</b>	1.5" (3.8 cm)
<b>Cutting Knives:</b>	Yes	<b>Knife Length:</b>	0.8" (2 cm)
<b>Cut Style:</b>	Side Cut	<b>Strips and Cuts AWG Solid:</b>	10-14
<b>Strips and Cuts AWG Stranded:</b>	12-16	<b>Screw Shearing:</b>	6-32, 8-32
<b>Joint Type:</b>	Solid	<b>Handle Color:</b>	Gray/Black
<b>Handle Finish:</b>	Journeyman™ Dual Material	<b>Handle Length:</b>	5" (13 cm)
<b>Insulated:</b>	No	<b>Tether Capable:</b>	No
<b>Weight:</b>	10.9 oz (308 g)		