

SWT

MECHANICAL THERMOSTAT – LINE VOLTAGE

COLOURS

- white, soft white

FINISH

- molded plastic

VOLTAGE

- 22 A @ 120-277 Vac
- 1/2 hp

CONTROL

- two-wire connection (single pole model) or four-wire connection (double pole model)
- temperature in degrees Celsius
- off position (double pole model)

TEMPERATURE RANGE

- 10 to 30 °C (50 to 90 °F)

WARRANTY

- one year



PRODUCT	DESCRIPTION
SWT1C*	SINGLE POLE THERMOSTAT (CELSIUS)
SWT2C	DOUBLE POLE THERMOSTAT (CELSIUS)

*Add SW for soft white.
Dimensions: 2 29/32 in. (74 mm) wide, 4 37/64 in. (116 mm) high and 1 9/64 in. (29 mm) deep



RJ32

MECHANICAL THERMOSTAT – LINE VOLTAGE

COLOURS

- white or beige

VOLTAGE

- 22 A @ 120, 208 or 240 Vac / 19 A @ 277 Vac

CONTROL

- two-wire connection (single pole model)
or four-wire connection (double pole model)
- temperature in degrees Celsius

TEMPERATURE RANGE

- 5 to 32 °C (41 to 90 °F)

WARRANTY

- one year



PRODUCT	DESCRIPTION	COLOUR
RJ32W1	SINGLE POLE THERMOSTAT	WHITE
RJ32B1	SINGLE POLE THERMOSTAT	BEIGE
RJ32W2	DOUBLE POLE THERMOSTAT	WHITE

Dimensions: 4 1/2 in. (114.3 mm) wide, 2 3/4 in. (69.9 mm) high and 2 1/4 in. (57.2 mm) deep



°STELPRO