SIRH | ZENITH™

INFRARED RADIANT HEATER







COMFORTABLY RADIANT!

Warm up your summer nights and autumn days with our Zenith infrared radiant heater. It's perfect for terraces, outdoor waiting areas, arenas and spas. It can even be used in hard-to-heat areas such as factories. With its 14-gauge aluminum cabinet and stainless steel grille, the Zenith is lightweight yet rugged. Now, you can create your own comfortable environment, any time of the year.

GENERATES INSTANT HEAT

COMPACT, LIGHTWEIGHT, STURDY AND EASY TO INSTALL

CLEAN ELECTRICAL ENERGY WITH NO AIR DISPLACEMENT

WEATHER-RESISTANT MODELS AVAILABLE

347 V MODEL AVAILABLE

COLOUR

• black

FINISH

 super-resistant polyester powdercoat

MANUFACTURING

- 14-gauge aluminum housing
- stainless steel grille
- specialized embossed aluminum reflectors that optimize radiant efficiency and reduce glare
- standard mounting bracket (included)

LAMP

- quartz lamp with glare-reducing filter and tungsten filament produces short-wave infrared heat
- 80% radiant efficiency

CONTROL

 electronic dimmer with timer (optional) (SIRHC402-1 or independent switch*)

INSTALLATION

 on wall or ceiling with mounting bracket (included) or pole mounted (adaptor not provided), in accordance with clearances and installation heights as specified in the installation manual

WARRANTY

- three years
- *The power feeding the units can be reduced using controls that meet the following requirements: the controls must be able to handle inductive and resistant loads. They must also have circuits to regulate the start-up current since this type of appliance generates a high start-up current.

IDEAL FOR:

terrace, warehouse, factory, outdoor waiting area, spa

FOR MAXIMUM EFFICIENCY

ELECTRONIC DIMMER WITH TIMER (OPTIONAL) SIRHC402-1







| TECHNICAL SPECIFICATIONS | | | | | | | | | | | | | |
|--------------------------|---------------|---------|-----------|---------|-----------|--------|-----|--------|----------|-------|-------|--------|------|
| PRODUC | T WEATHER-RES | SISTANT | POWER | VOLTAGE | FREQUENCY | LENGTH | | HEIGHT | | DEPTH | | WEIGHT | |
| CODE | CODE | | WATTS | VOLTS | HZ | MM | IN. | MM | IN. | MM | IN. | KG | LB |
| SIRH1501W | SIRH1501WR | | 1500 | 120 | 60 | 483 | 19 | 254 | 10 | 143 | 5 5/8 | 5 | 11 |
| SIRH2002W | SIRH2002WR | | 2000/1600 | 240/208 | 60 | 483 | 19 | 254 | 10 | 143 | 5 5/8 | 5 | 11 |
| SIRH4002W | SIRH4002WR | | 4000/3200 | 240/208 | 60 | 483 | 19 | 403 | 15 7/8 | 143 | 5 5/8 | 6.25 | 13.8 |
| SIRH4203W | SIRH4203WR | | 4180 | 347 | 60 | 483 | 19 | 554 | 21 13/16 | 143 | 5 5/8 | 7.4 | 16.3 |
| SIRH6002W | SIRH6002WR | | 6000/4800 | 240/208 | 60 | 483 | 19 | 554 | 21 13/16 | 143 | 5 5/8 | 7.4 | 16.3 |

| ACCESSORIES | | | | | |
|---------------|---|--|--|--|--|
| PRODUCT | DESCRIPTION | | | | |
| KIT-ESIRH151 | infrared replacement element 1500 W @ 120 V (SIRH1501 and SIRH4203 model) | | | | |
| KIT-ESIRH202 | infrared replacement element 2000 W/1600 W @ 240 V/208 V | | | | |
| KIT-SIRH-SUP1 | expandable support from 20 in. to 34 in. – 508 mm to 864 mm | | | | |
| SIRHC402-1 | electronic dimmer with timer (silver), 4000 W/3300 W/2000 W @ 240 V/208 V/120 V max | | | | |

TECHNICAL DRAWINGS







