

STZB402 | KI™ ZIGBEE

ELECTRONIC THERMOSTAT FOR SMART HOME

4000 W



CONNECTED COMFORT

The Ki Zigbee thermostat can easily be integrated into your home's Zigbee network, so you can adjust the temperature setpoint of rooms in your home from a distance.



**INTEGRATES EASILY
WITH A SMART HOME HUB**



**CONTROL WITH
A MOBILE APPLICATION**
DEPENDING ON HUB



ELECTRICITY SAVINGS
ENERGY SAVINGS OF 10-15%
DEPENDING ON USE*

COMPATIBILITY

- Maestro controller-thermostat or Zigbee hub required

COLOUR

- white

FINISH

- molded plastic

WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 300 W to 4000 W @ 240 V

CONTROL

- three functions available: comfort, economy and off
- two- or four-wire connection
- simple programming
- outdoor temperature display†
- compatible with forced-air units
- frost-free warning
- display in Celsius or Fahrenheit
- backlit screen with adjustable intensity
- activate several other functions

ACCURACY

- accurate ambient temperature control of ± 0.5 °C (1 °F)
- CSA C828-13
- temperature sensing with thermistor

TEMPERATURE RANGE

- 5 to 30 °C (41 to 86 °F)

WARRANTY

- three years

* independent study

† depending on the central controller and its application

COMPATIBLE WITH



TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	AMPERAGE	FREQUENCY	PACKAGING
	MINIMUM	MAXIMUM	VOLTS	AMPERES	HZ	
CODE						
STZB402WB+	150/300	2000/4000	120/240	16.7	50/60	BOX

Dimensions: 4 7/8 in. (124 mm) wide, 4 7/8 in. (124 mm) high and 1 3/8 in. (29 mm) deep

°STELPRO

For



FC_STZB402_EN_010520