

# TH140-28-01-B

ELECTRONIC THERMOSTAT – LINE AND LOW VOLT – 7-DAY PROGRAMMABLE

## COLOUR

- white

## FINISH

- molded plastic

## VOLTAGE

- Max: 5 A @ 24 V – 240 V resistive
- Max: 2 A @ 24 V – 240 V inductive

## CONTROL

- versatile thermostat that controls systems from millivolts to 240 V and is also well-suited for hot water heating
- battery powered (2 AA alkaline batteries)
- terminals R, W (X, C optional remote input)
- temperature sensing with thermistor

## TEMPERATURE RANGE

- 5 to 30°C (40 to 85°F)

## WARRANTY

- one year



PRODUCT	DESCRIPTION
TH140-28-01-B	ELECTRONIC PROG. THERMOSTAT, MILLIVOLT TO 240V, 5A RES. 2A IND.

Dimensions: 3 13/16 in. (97 mm) wide, 5 in. (127 mm) high and 1 in. (26 mm) deep



# TL116A1008

ELECTRONIC THERMOSTAT – LINE VOLTAGE

## COLOUR

- white

## FINISH

- molded plastic

## VOLTAGE

- Min: 1.5 A @ 120 V – 240 V
- Max: 12.5 A @ 120 V – 240 V

## CONTROL

- two-wire connection (single-pole model)
- temperature in degrees Celsius
- temperature sensing with thermistor

## TEMPERATURE RANGE

- 5 to 27°C (40 to 81°F)

## WARRANTY

- one year



PRODUCT	DESCRIPTION
TL116A1008	NON PROG. ELECTRONIC THERMOSTAT 3000W @ 240V

Dimensions: 3 1/32 in. (77 mm) wide, 5 in. (127 mm) high and 2 22/64 in. (60 mm) deep



°STELPRO