

FFI

FLOOR INSERT FAN HEATER



HEAT FROM AN UNEXPECTED PLACE

The FFI is the perfect solution when there's no wall space available, such as under low windows, bay windows and patio doors. It's also a great fit for offices, narrow entryways and bathrooms. It can be recessed between floor joists. Its grille is solidly constructed of rigid aluminum to withstand foot traffic. Installation at construction sites is easy thanks to its compact design. This floor insert fan heater can also be recessed into concrete floors.

DURABLE ALUMINUM GRILLE

EASILY CONCEALED

EASY INSTALLATION

CAN BE RECESSED INTO CONCRETE FLOORS

COLORS

- **standard:** white, soft white

FINISH

- epoxy-polyester powdercoat

MANUFACTURING

- durable 16-gauge steel cabinet and 9-gauge aluminum extruded grille
- protective wire mesh to prevent foreign objects from entering the interior of the unit
- 80 CFM capacity fan
- thermal protection with automatic reset

ELEMENT

- tubular element sheathed with spiral-wound fins for improved heat dissipation

CONTROL

- wall thermostat only (not included) – the use of an electronic thermostat is strongly recommended

INSTALLATION

- recessed between floor joists
- in a concrete floor without framing
- large wiring compartment

WARRANTY

- five years

IDEAL FOR:

in front of a patio door, office, narrow entryway, bathroom

°STELPRO



FC_FFI_US_270420



TECHNICAL SPECIFICATIONS

PRODUCT	POWER		VOLTAGE	THROW DISTANCE	HEAT RISE	WEIGHT
CODE	WATTS	BTU/H	VOLTS	FT	°F	LB
FFI1002	1000/750	3413	240/208	6'5"	108	18
FFI1502	1500/1125	5119	240/208	6'5"	119	18

Add W for white or SW for soft white

TECHNICAL DRAWINGS

