# **RE25 – RE30** ELECTRONIC RELAY - LOW VOLTAGE

### CONTROL

- pulsed signal (PWM) or all or nothing (on/off) at 24 Vac, 3-32 Vdc signal
- with a transformer (RE253T)
- compatible with the STE241, T822K1018U and T87K1007U thermostats
- two additional relays without transformers can be added to the same control circuit as a relay with a transformer
- installing more than four relays without transformers to the same thermostat is not recommended

# INSTALLATION

• the relay must be installed in an external junction box

# WARRANTY

• three years





1.	
9	RE306C

PRODUCT	DESCRIPTION
RE253C	ELECTRONIC LOW VOLTAGE RELAY [25 A @ 120 V, 208 V, 240 V, 277 V OR 347 V]
RE253T	ELECTRONIC LOW VOLTAGE RELAY [25 A @ 208 V, 240 V, 277 V OR 347 V] (W/TRANSFORMER)
RE306C	ELECTRONIC LOW VOLTAGE RELAY [30 A @ 120 V-600 V]

Dimensions: RE253: 4.10 in. x 4.10 in. x 2.10 in. / RE306C: 4.76 in. x 4.70 in. x 3 in.

# **RE15** ELECTRONIC RELAY - LOW VOLTAGE - SMALLER-SIZED

### CONTROL

- pulsed signal (PWM) or all or nothing (on/off) at 24 Vac, 3-32 Vdc signal
- with a transformer (RE153T)
- compatible with the STE241, T822K1018U and T87K1007U thermostats
- two additional relays without transformers can be added to the same control circuit as a relay with a transformer
- installing more than four relays without transformers to the same thermostat is not recommended

### INSTALLATION

WARRANTY • three years

• the relays must be installed inside the junction box of the heating unit





**RE156** 

**RE153** 

PRODUCT DESCRIPTION **RE153** ELECTRONIC LOW VOLTAGE RELAY [15 A @ 120 V-347 V] **RE156** ELECTRONIC LOW VOLTAGE RELAY [6 A @ 120 V-600 V] **RE153T** ELECTRONIC LOW VOLTAGE RELAY [15 A @ 208 V-347 V] (W/TRANSFORMER)

Dimensions: RE153 and RE156: 3.31 in. x 2.17 in. x 0.89 in. / RE153T: 3.31 in. x 2.17 in. x 1.5 in.





FC\_RE25-RE30-RE15\_US\_2105

