ST252NPFF - ST402NPFF

ELECTRONIC THERMOSTAT FOR FAN HEATERS

NON-PROGRAMMABLE















A WIND OF CHANGE!

Stelpro's all-new non-programmable electronic thermostats designed specifically for fan heaters let you make the most of your comfort thanks to advanced features such as "Boost" and "Lobby" modes. Harmonious design, superior technology and safe operation merge to ensure your comfort in all circumstances.

ENERGY SAVINGS UP TO 12%*

ECO MODE

ONE-CLICK TEMPERATURE SETBACK

HEAT "BOOST" FEATURE

RAPID TEMPERATURE RISE

LOBBY MODE

COMPENSATES FOR FAST TEMPERATURE DROPS

SAFE DESIGN

SEALED HOUSING

S³ MOUNTING PLATE

STURDY, SIMPLE AND SAFE INSTALLATION

COLOR

white

FINISH

molded plastic

WATTAGE AND VOLTAGE

ST252NPFF

- 150 W to 1250 W @ 120 V
- 260 W to 2160 W @ 208 V
- 300 W to 2500 W @ 240 V

ST402NPFF

- 150 W to 2000 W @ 120 V
- 260 W to 3475 W @ 208 V
- 300 W to 4000 W @ 240 V

CONTROL

- three-wire connection
- compatible with forced-air units
- eco mode: One-click temperature setback
- maximum power when "boost" mode is activated (with a timer)
- display in Celsius or Fahrenheit

ACCURACY

- accurate ambient temperature control of ± 1°F
- CSA C828-13
- temperature sensing with thermistor

TEMPERATURE RANGE

• 41 to 86 °F

WARRANTY

- three years
- * independent study

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		TENSION	MAX. AMPERAGE	FREQUENCY	PACKAGING
CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	HZ	
ST252NPFF	150/260/300	1250/2160/2500	120/208/240	10.4	60	BOX
ST402NPFF	150/260/300	2000/3475/4000	120/208/240	16.7	60	BOX

DIMENSIONS ST252NPFF: 4,35 in. wide, 4,94 in. high and 1,38 in. deep DIMENSIONS ST402NPFF: 4,94 in. wide, 4,94 in. high and 1,38 in. deep



