

ST302P – ST402P

ELECTRONIC THERMOSTATS FOR BASEBOARDS AND CONVECTORS

PROGRAMMABLE



3000 W



4000 W



CUSTOMIZED COMFORT IN THREE EASY STEPS

Harmonious design, superior technology and safe operation merge in Stelpro's all-new programmable electronic thermostats for baseboards and convectors. With simple three-step programming, you can manage your home's comfort while enjoying energy savings up to 20% compared to a mechanical thermostat and up to 8%* compared to a non-programmable thermostat.

ENERGY SAVINGS UP TO 20%*

SIMPLE THREE-STEP PROGRAMMING

UNBEATABLE ACCURACY

QUALITY SENSORS AND ADVANCED ALGORITHMS

SAFE DESIGN

SEALED HOUSING

S³ MOUNTING PLATE

STURDY, SIMPLE AND SAFE INSTALLATION

COLOR

- white

FINISH

- molded plastic

WATTAGE AND VOLTAGE

ST302P

- 150 W to 1500 W @ 120 V
- 260 W to 2600 W @ 208 V
- 300 W to 3000 W @ 240 V

ST402P

- 150 W to 2000 W @ 120 V
- 260 W to 3475 W @ 208 V
- 300 W to 4000 W @ 240 V

CONTROL

- two-wire connection
- possibility of four events on weekdays and two events on weekends
- protection against power failure (two hours)
- display in Celsius or Fahrenheit

ACCURACY

- accurate ambient temperature control of $\pm 1^{\circ}\text{F}$
- CSA C828-13
- temperature sensing with thermistor

TEMPERATURE RANGE

- 41 to 86 $^{\circ}\text{F}$

WARRANTY

- three years

* independent study

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	MAX. AMPERAGE	FREQUENCY	PACKAGING
CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	HZ	
ST302P	150/260/300	1500/2600/3000	120/208/240	12.5	60	BOX
ST402P	150/260/300	2000/3475/4000	120/208/240	16.7	60	BOX

DIMENSIONS ST302P: 4,35 in. wide, 4,94 in. high and 1,38 in. deep
DIMENSIONS ST402P: 4,94 in. wide, 4,94 in. high and 1,38 in. deep

°STELPRO



FC_ST302-ST402_P_US_280420