

ST402PFF

ELECTRONIC THERMOSTAT FOR FAN HEATERS

PROGRAMMABLE



4000 W



STAY IN TUNE WITH THE TIMES!

This new programmable electronic thermostat designed specifically for fan heaters lets you make the most of your comfort thanks to advanced features such as “Boost” and “Lobby” modes. With simple three-step programming, you can manage your home’s comfort while enjoying energy savings up to 20% compared to a mechanical thermostat.

ENERGY SAVINGS UP TO 20%*

SIMPLE THREE-STEP PROGRAMMING

HEAT “BOOST” FEATURE QUICK TEMPERATURE RISE

“LOBBY” MODE COMPENSATES FOR FAST TEMPERATURE DROPS

SAFE DESIGN SEALED HOUSING

S³ MOUNTING PLATE STURDY, SIMPLE AND SAFE INSTALLATION

COLOR

- white

FINISH

- molded plastic

WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 260 W to 3475 W @ 208 V
- 300 W to 4000 W @ 240 V

CONTROL

- three-wire connection
- maximum power when “boost” mode is activated (with a timer)
- possibility of four events on weekdays and two events on weekends
- protection against power failure (two hours)
- display in Celsius or Fahrenheit

ACCURACY

- accurate ambient temperature control of $\pm 1^\circ\text{F}$
- CSA C828-13
- temperature sensing with thermistor

TEMPERATURE RANGE

- 41 to 86 °F

WARRANTY

- three years

* independent study

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	MAX. AMPERAGE	FREQUENCY	PACKAGING
	CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	
ST402PFF	150/260/300	2000/3475/4000	120/208/240	16.7	60	BOX

DIMENSIONS ST402PFF : 4,94 in. wide, 4,94 in. high and 1,38 in. deep

°STELPRO



FC_ST402_PFF_US_130620