

# SCRG

## CONSTANT WATTAGE ROOF AND GUTTER DE-ICING HEATING CABLE



### LESS WEIGHT ON YOUR ROOF

This preassembled heating cable is designed to prevent ice damming on roofs and gutters, which could be harmful to the roof and dangerous for passers-by.\* The roof and gutter de-icing cable creates a path that allows water to flow normally through the gutters. It's easy to install on any type of inclined roof. It can also be installed in metal or plastic gutters.

#### PREVENT ROOF DAMAGE AND LEAKING

#### KEEP GUTTERS AND DOWNSPOUTS FLOWING

#### PREASSEMBLED READY TO INSTALL

#### THERMOSTAT WITH TEMPERATURE AND MOISTURE SENSORS (OPTIONAL)

#### MANUFACTURING

- tough XLPE inner insulation
- continuous ground braid
- weather resistant PVC (high-low temperature) out jacket
- twin conductor
- bending radius of 1 inch
- 6 ft cold lead with plug

#### WATTAGE

- 5 W/ft

#### CONTROL

- controller with moisture and ambient temperature sensors (optional)

#### INSTALLATION

- install at a temperature above 32 °F

#### WARRANTY

- two years

\*Never install on a flat roof. This cable is not designed to remove all the snow from a roof.



QUICK PLUG-IN INTO RESIDENTIAL 120 V OUTLET

#### IDEAL FOR:

roofs and gutters with ice damming problems

#### FOR MAXIMUM EFFICIENCY

#### CONTROLLER WITH MOISTURE AND AMBIENT TEMPERATURE SENSORS (OPTIONAL)



# TECHNICAL SPECIFICATIONS

PRODUCT	LENGTH	POWER	AMPERAGE
CODE	FT	WATTS	AMPS
120 VOLTS			
SCRG1W0150L0030	30	150	1.3
SCRG1W0300L0060	60	300	2.5
SCRG1W0400L0080	80	400	3.3
SCRG1W0500L0100	100	500	4.2
SCRG1W0600L0120	120	600	5.0
SCRG1W0800L0160	160	800	6.7
SCRG1W1000L0200	200	1000	8.3
SCRG1W1200L0240	240	1200	10.0

# ACCESSORY

PRODUCT	DESCRIPTION
SCRG-CONTROL	control for SCRG cable with moisture and ambient temperature sensors (120 V @ 10 A)

