

# SORB | ORLÉANS™

HIGH-END FAN HEATER FOR BATHROOMS



ORLÉANS™



## FOR FAST COMFORT!

The Stelpro family of high-end Orléans convectors is growing. Treat yourself to our brand-new Orléans high-end fan heater and enjoy a toasty warm bathroom even in winter. Thanks to its optimum heat output and rapid temperature rise, this model provides heat exactly when you need it. It is also the quietest fan heater in its category, allowing you to relax and enjoy some peace and quiet. Very similar to our Orléans high-end convector, this fan heater has an optional built-in, smart-home-ready thermostat.

### THE QUIETEST FAN HEATER IN ITS CATEGORY

### HEAT “BOOST” MODE FAST TEMPERATURE RISE (1000 W TO 2000 W)†

### STURDY, DURABLE AND RUST-RESISTANT

### OPTIONAL BUILT-IN ELECTRONIC THERMOSTAT PERFECT FOR THE SMART HOME

### COLOURS

- **standard:** white, soft white

### FINISH

- epoxy-polyester powdercoat

### MANUFACTURING

- high performance polymer cabinet, 20-gauge satin-finish steel front with moulded aluminum edges
- centrifugal fan that ensures a quiet and efficient airflow
- thermal protections with manual reset
- top front air intake and bottom front air discharge

### ELEMENT

- high-quality nichrome element that generates instant heat

### CONTROL

- MODEL WITHOUT A THERMOSTAT:
- an electronic wall thermostat is recommended

### MODEL WITH A BUILT-IN THERMOSTAT:

- built-in Maestro smart thermostat featuring the Zigbee protocol
- 1000 W to maintain temperature setpoint
- 2000 W when “boost” mode is activated (with a timer)
- colour-code feedback for responsible energy consumption
- drastic temperature drop detection (open window function)

### INSTALLATION

- recessed or surface mounted – surface adaptor included
- on the wall, a minimum of 6 in. from the floor
- front easy to install with only one mounting screw
- power switch selector – 1000 W or 2000 W (model without a thermostat only)

### WARRANTY

- five years, \*three years on electronic components

† 5°C (9°F) temperature rise within five minutes. (Tests performed with the 2000 W model in a 70 ft² room.)


### IDEAL FOR:

bathroom, entrance, vestibule, hallway, living space

### PART OF THE ORLÉANS FAMILY OF PRODUCTS

NEED A CONVECTOR?

SOR



°STELPRO



FC\_SORB\_EN\_210720




## TECHNICAL SPECIFICATIONS

PRODUCT	THERMOSTAT HEATING	TIMER HEATING	WITHOUT THERMOSTAT	VOLTAGE	HEIGHT		LENGTH		WEIGHT	
	WATTS	WATTS	WATTS		MM	IN.	MM	IN.	KG	LB
SORB2002M	1000/750	2000/1500	---	240/208	398	15 11/16	322	12 11/16	4.3	9.4
SORB2002WC	---	---	2000/1500 OR 1000/750*	240/208	398	15 11/16	322	12 11/16	4.3	9.4

Add W for white or SW for soft white \* Selected when installed with a power switch

## TECHNICAL DRAWINGS



### BUILT-IN THERMOSTAT

CONTROL THE TEMPERATURE OF YOUR HOME FROM YOUR SMARTPHONE, TABLET OR COMPUTER



**zigbee** COMPATIBLE CONTROLLER REQUIRED

HARMONIZES WITH  
**MAESTRO**

WORKS WITH  
**SmartThings**