

# ST302P – ST402P

## ELECTRONIC THERMOSTATS FOR BASEBOARDS AND CONVECTORS

PROGRAMMABLE



3000 W

4000 W



### CUSTOMIZED COMFORT IN THREE EASY STEPS

Harmonious design, superior technology and safe operation merge in °STELPRO's all-new programmable electronic thermostats for baseboards and convectors. With simple three-step programming, you can manage your home's comfort while enjoying energy savings up to 20% compared to a mechanical thermostat and up to 8%\* compared to a non-programmable thermostat.

#### ENERGY SAVINGS UP TO 20%\*

#### SIMPLE THREE-STEP PROGRAMMING

#### UNBEATABLE ACCURACY

QUALITY SENSORS AND ADVANCED ALGORITHMS

#### SAFE DESIGN

SEALED HOUSING

#### S<sup>3</sup> MOUNTING PLATE

STURDY, SIMPLE AND SAFE INSTALLATION

#### COLOUR

- white

#### FINISH

- molded plastic

#### WATTAGE AND VOLTAGE

##### ST302P

- 150 W to 1500 W @ 120 V
- 260 W to 2600 W @ 208 V
- 300 W to 3000 W @ 240 V

##### ST402P

- 150 W to 2000 W @ 120 V
- 260 W to 3475 W @ 208 V
- 300 W to 4000 W @ 240 V

#### CONTROL

- two-wire connection
- possibility of four events on weekdays and two events on weekends
- protection against power failure (two hours)
- display in Celsius or Fahrenheit

#### ACCURACY

- accurate ambient temperature control of  $\pm 0.5$  °C (1°F)
- CSA C828-13
- temperature sensing with thermistor

#### TEMPERATURE RANGE

- 5 to 30 °C (41 to 86 °F)

#### WARRANTY

- three years

\* independent study

### TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	MAX. AMPERAGE	FREQUENCY	PACKAGING
CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	HZ	
ST302P	150/260/300	1500/2600/3000	120/208/240	12.5	60	BOX
ST402P	150/260/300	2000/3475/4000	120/208/240	16.7	60	BOX

DIMENSIONS ST302P: 4,35 in. (110,5 mm) wide, 4,94 in. (125,5 mm) high and 1,38 in. (35 mm) deep  
DIMENSIONS ST402P: 4,94 in. (125,5 mm) wide, 4,94 in. (125,5 mm) high and 1,38 in. (35 mm) deep

°STELPRO

