

# SMT402 | MAESTRO™

SMART THERMOSTAT

4000 W

## MAESTRO™

DESIGNED FOR:



## ORCHESTRATING COMFORT

Use the MAESTRO thermostat with the MAESTRO controller•thermostat to turn your house into a smart home in a snap! Indeed, the MAESTRO thermostat reveals its full potential when it's paired with the MAESTRO controller•thermostat. It can also be linked to an existing Zigbee network controlled by any Zigbee-compatible controller. Maestro is the smart home comfort solution!



**COMPATIBLE WITH MAESTRO CONTROLLER OR ZIGBEE HUB**  
CONTROL AT YOUR FINGERTIPS WITH YOUR SMARTPHONE OR MOBILE DEVICE



**RELATIVE ROOM HUMIDITY DISPLAY**



**ENERGY CONSUMPTION ASSESSMENT†**  
FOR OPTIMAL ENERGY EFFICIENCY



**ELECTRICITY SAVINGS**  
ENERGY SAVINGS UP TO 25%  
DEPENDENT ON USE\*

### COMPATIBILITY

- MAESTRO controller•thermostat or Zigbee hub required

### COLOUR

- white

### FINISH

- molded plastic

### WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 260 W to 3400 W @ 208 V
- 300 W to 4000 W @ 240 V

### CONTROL

- two- or four-wire connection
- MAESTRO environment options include:
  - outdoor temperature or relative room humidity display
  - energy consumption assessment

- lock screen capability
- screen backlighting
- radical temperature decrease detection (open-window feature)
- motion-activated screen
- Zigbee home automation environment compatibility

### ACCURACY

- accurate ambient temperature control of  $\pm 0.5^{\circ}\text{C}$  ( $1^{\circ}\text{F}$ )
- CSA C828-13

### TEMPERATURE RANGE

- 5 to  $30^{\circ}\text{C}$  (41 to  $86^{\circ}\text{F}$ )

### WARRANTY

- three years

† with MAESTRO ecosystem

\* study carried out by an independent university team

## ACCESSORIES

PRODUCT	DESCRIPTION
SMAMPLIZB	Zigbee signal amplifier
SMREPETZB	Zigbee signal repeater

### COMPATIBLE WITH



## MAESTRO™

FOR HOME AUTOMATED SYSTEM COMPATIBILITIES AND INSTRUCTIONS ON CONNECTING TO YOUR MAESTRO THERMOSTAT, VISIT [WWW.STELPRO.COM/MAESTRO](http://WWW.STELPRO.COM/MAESTRO).

## TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	AMPERAGE	FREQUENCY	COLOUR	PACKAGING
CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	HZ		
SMT402	150/260/300	2000/3400/4000	120/208/240	16.7	50/60	WHITE	BOX

Dimensions: 5 3/8 in. (137 mm) wide, 5 3/8 in. (137 mm) high and 1 1/4 in. (32 mm) deep

# °STELPRO

