

RUH | OXFORD™

COMMERCIAL AND RESIDENTIAL UNIT HEATER



OXFORD™
SERIES | SÉRIE



A VERSATILE WORKHORSE

The RUH unit heater is small on price and big on heat. These heavy-duty units are well suited to situations where large amounts of heat must be provided in wide open spaces such as garages, workshops, commercial warehouses and construction sites. This unit has a powerful output up to 5000 W with a voltage of 240/208. The RUH has adjustable louvers that allow you to direct heat right from the source. With or without a built-in thermostat, it provides instant heat. Quiet, lightweight and easy-to-install with a universal wall or ceiling mounting bracket, this unit heater is everything you expect for less. Guaranteed productivity!

INSTANT HEAT

ADJUSTABLE LOUVERS ALLOW YOU TO DIRECT HEAT

WALL OR CEILING INSTALLATION SUPPORT BRACKET INCLUDED

ENCLOSED AND PERMANENTLY LUBRICATED MOTOR

2 KW TO 5 KW MODELS AVAILABLE

COLOUR

- charcoal

FINISH

- epoxy-polyester powdercoat

MANUFACTURING

- 20-gauge steel cabinet
- totally enclosed and factory lubricated motor
- 350 CFM quiet helicoidal fan
- adjustable louvers
- thermal protection with automatic reset

ELEMENT

- nichrome element produces instant heat

CONTROL

- built-in thermostat (included with T series)
- wall thermostat (not included)

INSTALLATION

- wall or ceiling mounted with universal mounting bracket (included with unit)

WARRANTY

- three years

IDEAL FOR:

construction site, garage, workshop, small commercial space

°STELPRO





TECHNICAL SPECIFICATIONS

WITHOUT CONTROL	BUILT-IN THERMOSTAT	24 V CONTROL	POWER	VOLTAGE	FLOW	THROW DISTANCE		HEAT RISE		WEIGHT	
CODE	CODE	CODE	WATT S	VOLTS	CFM	M	FT.	°C	°F	KG	LB
RUH2CHAR	RUH2TCHAR	RUH2C24CHAR	2000/1500	240/208	350	3	10	27	48	9	20
RUH3CHAR	RUH3TCHAR	RUH3C24CHAR	3000/2250	240/208	350	3	10	34	60	9	20
RUH4CHAR	RUH4TCHAR	RUH4C24CHAR	4000/3000	240/208	350	3	10	46	82	9	20
RUH5CHAR	RUH5TCHAR	RUH5C24CHAR	5000/3750	240/208	350	3	10	64	114	9	20

TECHNICAL DRAWINGS

