

D010

ELECTRONIC THERMOSTAT – LOW VOLTAGE / 24 V

COLOUR

- off-white

VOLTAGE

- 1 A @ 24 Vac

CONTROL

- three-wire connection
- all or nothing @ 24 Vac
- compatible with all RE, RM and R841D1036 model relays
- temperature in degrees Celsius and Fahrenheit

TEMPERATURE RANGE

- 10 to 30 °C (50 to 86 °F)

WARRANTY

- one year



PRODUCT	DESCRIPTION
D010	24 V THER MOSTAT

Dimensions : 3.54 in. x 3.54 in. x 1.57 in. (89.9 mm x 89.9 mm x 39.9 mm)



ET180

ELECTRONIC THERMOSTAT – LOW VOLTAGE / 24 V

COLOUR

- off-white

VOLTAGE

- 1 A @ 24 Vac
- display powered by batteries (2 X AAA – not provided)

CONTROL

- two-wire connection
- all or nothing (NO or NC)
- compatible with all RE, RM and R841 model relays
- temperature in degrees Celsius

TEMPERATURE RANGE

- 5 to 35 °C (40 to 95 °F)

WARRANTY

- one year



PRODUCT	DESCRIPTION
ET180	24 V ELECTRONIC THERMOSTAT

Dimensions : 3.27 in. x 3.27 in. x 1.19 in. (83.1 mm x 83.1 mm x 30.2 mm)

