

STZW402 | KI™ Z-WAVE

ELECTRONIC THERMOSTAT FOR SMART HOME

4000 W



CONNECTED COMFORT

KI Z-Wave thermostats can easily be integrated into your home's Z-Wave network, so you can adjust the temperature setpoint of rooms in your home from a distance.



**INTEGRATES EASILY
WITH A SMART HOME HUB**



**CONTROL WITH
A MOBILE APPLICATION**
DEPENDING ON THE HUB



ELECTRICITY SAVINGS
ENERGY SAVINGS OF 10-15%
DEPENDING ON USE*

COMPATIBILITY

- Z-Wave hub required
- Z-Wave Plus certified

COLOUR

- white

FINISH

- molded plastic

WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 300 W to 4000 W @ 240 V

CONTROL

- two functions available: comfort and economy
- two- or four-wire connection
- outdoor temperature display†
- frost-free warning
- display in Celsius or Fahrenheit
- backlit screen with adjustable intensity

ACCURACY

- accurate ambient temperature control of ± 0.5 °C (1 °F)
- CSA C828-13
- temperature sensing with thermistor

TEMPERATURE RANGE

- 5 to 30 °C (41 to 86 °F)

WARRANTY

- three years

* independent study

† depending on the central controller and its application

COMPATIBLE WITH



WORKS WITH
SmartThings

FOR HOME AUTOMATED SYSTEM COMPATIBILITIES AND INSTRUCTIONS ON CONNECTING TO YOUR KI THERMOSTAT, VISIT WWW.STELPRO.COM.

TECHNICAL SPECIFICATIONS

| PRODUCT | WATTS | | VOLTAGE | AMPERAGE | FREQUENCY | PACKAGING |
|------------|---------|-----------|---------|----------|-----------|-----------|
| CODE | MINIMUM | MAXIMUM | VOLTS | AMPERES | HZ | |
| STZW402WB+ | 150/300 | 2000/4000 | 120/240 | 16.7 | 50/60 | BOX |

Dimensions: 4 7/8 in. (124 mm) wide, 4 7/8 in. (124 mm) high and 1 3/8 in. (29 mm) deep

°STELPRO



