

ASMT402 | MAESTRO™

SMART THERMOSTAT

4000 W

MAESTRO™

DESIGNED FOR:



ORCHESTRATING COMFORT

Use the MAESTRO thermostat with the MAESTRO controller•thermostat to turn your house into a smart home in a snap! Indeed, the MAESTRO thermostat reveals its full potential when it's paired with the MAESTRO controller•thermostat. It can also be linked to an existing Zigbee network controlled by any Zigbee-compatible controller. Maestro is the smart home comfort solution!



COMPATIBLE WITH MAESTRO CONTROLLER OR ZIGBEE HUB
CONTROL AT YOUR FINGERTIPS WITH YOUR SMARTPHONE OR MOBILE DEVICE



RELATIVE ROOM HUMIDITY DISPLAY



ENERGY CONSUMPTION ASSESSMENT†
FOR OPTIMAL ENERGY EFFICIENCY



ELECTRICITY SAVINGS
ENERGY SAVINGS UP TO 25% DEPENDING ON USE*

COMPATIBILITY

- MAESTRO controller•thermostat or Zigbee hub required

COLOR

- white

FINISH

- molded plastic

WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 260 W to 3400 W @ 208 V
- 300 W to 4000 W @ 240 V

CONTROL

- two- or four-wire connection
- MAESTRO environment options include:
 - outdoor temperature or relative room humidity display
 - energy consumption assessment

- lock screen capability
- screen backlighting with light intensity setting
- radical temperature decrease detection (open-window feature)
- motion-activated screen
- Zigbee home automation environment compatibility

ACCURACY

- accurate ambient temperature control of ± 1 °F
- CSA C828-13

TEMPERATURE RANGE

- 41 to 86 °F

WARRANTY

- three years

† with MAESTRO ecosystem

* study carried out by an independent university team

ACCESSORIES

PRODUCT	DESCRIPTION
SMAMPLIZB	Zigbee signal amplifier
SMREPETZB	Zigbee signal repeater

COMPATIBLE WITH



MAESTRO™

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	AMPERAGE	FREQUENCY	COLOR	PACKAGING
	CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	HZ	
ASMT402		150/260/300	2000/3400/4000	120/208/240	16.7	50/60	WHITE BOX

Dimensions: 5 3/8 in. wide, 5 3/8 in. high and 1 1/4 in. deep

°STELPRO



FC_SMT402_140618