

SOA | OASIS™

FAN HEATER FOR BATHROOMS



oasis™

GRANDS
PRIX
DU DESIGN



MAKE YOUR BATHROOM AN OASIS OF PEACE AND TRANQUILITY

The quiet and discreet OASIS bathroom fan heater provides all the comfort you need. It features a highly accurate electronic thermostat and optimal heat output, so you can easily and rapidly control the comfort-level of your rooms. Also offered without a thermostat, it's the perfect little device to heat small rooms like vestibules or hallways. In addition, its refined look and high-performance polymer finish blend in with any decor.

ULTRA-QUIET FAN HEATER

HEAT "BOOST" MODE

FAST TEMPERATURE INCREASE
(1000 W TO 2000 W) †

FEATURING HIGH-PERFORMANCE POLYMER AND SATIN-FINISH PAINTED STEEL

OPTIONAL BUILT-IN ELECTRONIC THERMOSTAT

COLOUR

- white

FINISH

- epoxy-polyester powdercoat

MANUFACTURING

- high performance polymer cabinet and front edges, 20-gauge satin-finish steel front
- centrifugal fan that ensures a quiet and efficient airflow
- thermal protection with automatic reset
- additional thermal protection with a thermal fuse (must be replaced if triggered)
- top front air intake and bottom front air discharge

ELEMENT

- high-quality nichrome element that generates instant heat

CONTROL

MODEL WITH A BUILT-IN THERMOSTAT:

- built-in electronic thermostat
- 1000 W to maintain temperature setpoint
- 2000 W when "boost" mode is activated (with a timer)
- drastic temperature drop detection (open window function)

MODEL WITHOUT A THERMOSTAT:

- an electronic wall thermostat is recommended

INSTALLATION

- recessed or surface mounted – surface adapter not required
- on the wall, a minimum of 6 in. from the floor
- front easy to install with only one mounting screw
- power switch selector – 1000 W or 2000 W (model without a thermostat only)

WARRANTY

- five years, *three years on electronic components

† 5°C (9°F) temperature rise within five minutes. (Tests performed with the 2000 W model in a 70 ft² room.)



ALSO AVAILABLE

QUICK PLUG-IN INTO
RESIDENTIAL 120 V OUTLET

IDEAL FOR:

bathroom, entrance, vestibule, hallway,
living space

°STELPRO





TECHNICAL SPECIFICATIONS

PRODUCT	THERMOSTAT HEATING	TIMER HEATING	WITHOUT THERMOSTAT	VOLTAGE	HEIGHT	LENGTH	WEIGHT			
CODE	WATTS	WATTS	WATTS	VOLTS	MM	IN.	MM	IN.	KG	LB
SOA2002W	1000/750	2000/1500	---	240/208	402	15 13/16	305	12	3.6	7.9
SOA2002WCW	---	---	2000/1500 OR 1000/750*	240/208	402	15 13/16	305	12	3.6	7.9
MODEL WITH 120 V PLUG (RESIDENTIAL OUTLET)										
SOA1501PW	1000	1500	---	120	402	15 13/16	305	12	3.6	7.9

* Select when installing with a power switch

TECHNICAL DRAWINGS

