SATCO' NUVO

Project Name

Location

Prepared By



6G25/LED/WH/940/120V

Notes

General Status Active Watts 6W 60W Incandescent Equivalent Volts 120V Shape G25 Base Medium ANSI Base E26 Finish White CCT (Kelvin) 4000K Temperature Cool White CRI 90 Lumens 500L Beam Spread 320 Dimmable Yes-Dimmable Hours Rated 15000 LED Technology Electrical **Operating Frequency** 60 Hz >0.7 Power Factor -20C (-4F) to a maximum of +45C **Operating Temperature** (+113F) Physical MOL 4.45 MOD 3.15 Weight (lb.) 0.088 Additional Information Rated For Enclosed Fixture Yes Warranty 3 Year Limited Compliance cETLus Safety Listing Location Rating Wet Pending Energy Star CA T20 / T24 Rationale T20 Listed California Status Lawful for sale in California Title 20 / 24 Status Lawful for sale

Yes

For More Information Visit: <u>http://www.satco.com/</u>

RoHS Compliant

