RMSM

Approvals:

SP


PAR18 MINI REMOTE


CSA Certified to C22.2 #141.15

Plastic Construction Single, Double or Triple 6V, 12V & 24V Lamps in LED, Quartz & Tungsten



DIMENSIONS





The RMSM series of commercial thermoplastic PAR18 remotes provides the perfect balance of value and performance. The heads are fully adjustable and both tilt and swivel are lockable. The standard canopy is designed to mount directly to typical electrical junction boxes. Available in 6V, 12V and 24V models, utilizing either LED (bi-pin based), tungsten (wedge based) or quartz halogen (bi-pin based) lamps.

MECHANICAL

DESCRIPTION

- UV stabilized, high impact thermoplastic, composite head construction
- Fully adjustable both tilt and swivel
- 5" diameter thermoplastic canopy standard
- Two recessed canopy mounting holes designed to match standard electrical junction boxes
- White color is standard, black is optional
- Variety of lamp options:
 - 6VDC, 12VDC or 24VDC
 - Tungsten lamps wedge based
 - Quartz halogen lamps bi-pin based
 - LED lamps bi-pin based

AimLite's LED current technology ensures the lumens output remains constant throughout the battery's discharge whether at 6V or 12V applications.

ORDERING GUIDE - LED

RMSM

					·	
Series	Number of heads	Voltage	Wattage	Lamp type	Color	Options [†]
	 1 - Single head 2 - Double head 3 - Triple head 4 - Quad head (require 12" dia. canopy) 	6-12 - 6VDC to 12VDC operational	3W - 3 watts 4W - 4 watts	lj - Led	WHT - White (standard) BLK - Black	LCP, VDR, WRG, LXG
		6-24 - 6VDC to 24VDC operational	5W - 5 watts	la - Led		
		12-24 - 12VDC to 24VDC operational	6W - 6 watts 7W - 7 watts	LA - LED		
		24 - 24VDC	4W - 4 watts	LR - LED		

† For detailed options descriptions, please consult the options page

ORDERING GUIDE - INCANDESCENT

RMSM	-	_			/
Series	Number of heads	Voltage	Lamp	Color	Options ⁺
RMSM	1 - Single head 2 - Double head 3 - Triple head 4 - Quad head (require 12" dia. canopy)	06V - 6VDC 12V - 12VDC 24V - 24VDC	See lamp selection chart below	WHT - White (standard) BLK - Black	LCP, VDR, WRG, LXG

LAMP SELECTION - INCANDESCENT

	6 Volts	12 Volts	24 Volts					
PAR18 - Small He	AR18 - Small Head							
Quartz halogen	08Q, 10Q, 12Q	08Q, 10Q, 12Q	12Q					
Tungsten	09T	9T, 18T	9T, 18T					

† For detailed options descriptions, please consult the options page.

