



BURNDY Catalog Number	BIBS2/04
UPC Number	781810223895
Description	2/0-14 ONE SIDED UNITAP
Status	Active

Web Use  
BURNDY Product Line

Dimensional	
Width (in)	1.31
Hex Size (Key)	3/16
Length (in)	2.86
Height (in)	1.38
Electrical	
Min Voltage Rating	600
General	
Number of Ports	4
Number of Screws	4
Product Description	Aluminum Multiple Tap Connector, Clear Insulated, 4 Port, 1 Sided Entry, 14-2/0 AWG, Al/Cu Rated
Conductor(s)	
Aluminum Size (Range)	8 AWG-2/0 AWG
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	14 AWG-2/0 Str
Physical	
Type of Hardware	Aluminum
Type of Plating	Unplated
Insulation Type	Plastisol
Plated (Yes or No)	N
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA  
47, industrial Park Drive  
Manchester NH03109

BURNDY Technical Servcies  
47, industrial Park Drive  
Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
Monday - Friday  
Phone: 000-346-4175