



BURNDY Catalog Number	BISR3/0DB
UPC Number	781810288030
Description	3/0-1/0 DIRECTBURIALUNIT
Status	Active

Web Use
BURNDY Product Line

Dimensional	
Screw Size	7/16
Width (in)	0.99
Hex Size (Key)	3/16
Length (in)	6.25
Height (in)	1.96
Electrical	
Min Voltage Rating	600
General	
Number of Ports	2
Number of Screws	2
Product Description	In-Line Splice/Reducer, 2 Port, 1/0-3/0 AWG, Al/Cu Rated
Conductor(s)	
Aluminum Size (Range)	1/0-3/0 AWG
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	1/0 -3/0 AWG
Physical	
Type of Hardware	Aluminum
Installation Torque	220
Type of Plating	Unplated
Insulation Type	Plastisol
Plated (Yes or No)	N
Product Material	Aluminum
Approvals / Certifications	
UL Listed	Y
CSA Certified	N
Rated for Direct Burial	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies
47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175