NEER Zinc Two Screw Connectors

For Nonmetallic Sheathed Cable

C: Two Screw

Application

• Open throat type for nonmetallic sheathed cable.

Features

- Furnished with locknut.
- Male hub threads NPS.

Standard Material/Finish


- Body: zinc diecast
- Clamp: steel/zinc plated Screw: steel/zinc plated

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E25015
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 208044
- NEMA: FB-1

Note:

• All connectors listed for use with a single cable only except for the C-500 which is also listed for use with two 14-2 AWG or two 12-2 AWG NM cables. C-500 also listed for flexible cord with a diameter range of 0.29in./ 7.4mm. to 0.45in./11.4mm.



Trade Size	Catalog	Dimensions in Inches/Millimeters			Nm Cable
(Inches)	Number	Α	В	C	Range
3/8 (1/2 knockout)	C-500	0.36/ 9.1	0.81/ 20.6	0.91/ 23.1	14-2 to 12-2
3/4	C-750	0.42/ 10.7	0.94/ 23.9	1.20/ 30.5	10-3 to 8-2
1	C-1001-R	0.51/ 13.0	1.11/ 28.2	1.51/ 38.4	10-3 to 4-2

