

HDMI Cables



MAKE ALL THE DIFFERENCE WITH THE RIGHT CABLES.

Premium High Speed HDMI Cables with Ethernet

A vital component in successfully delivering high quality content is the HDMI cable. The Premium HDMI Cable Certification Program is a new verification platform from the creators of HDMI technology. It encompasses additional testing as well as authentication and verification to ensure cables support the full 18Gbps bandwidth from the HDMI 2.0b specification. Certified cables feature packaging with the official Premium HDMI Certification label and QR Code to verify authenticity.

Tri-Rated for Residential and Commercial Use

The entire selection of On-Q in-wall HDMI cables are CMG, CL3, and FT4 rated – and clearly labeled – to provide reliable pro-grade cables that meet any residential or commercial installation's standards.

Flexible Slimline Options

Perfect for outside the wall connections, the Slimline HDMI cables from Legrand come in short lengths and clean white casing, and are 75% thinner than regular HDMI cables, for the most professional-looking installations.

FEATURES

- Full range of passive, active, in-wall, and Slimline High Speed HDMI cables, with Ethernet connectivity, available
- In-wall cables are CMG, CL3, and FT4-rated for reliable use in residential or commercial environments
- Slimline cables offer an uncluttered professional look for shorter connections outside of walls
- Premium HDMI cables have been tested and certified to support the full 18Gbps bandwidth from the 2.0b specification for 4K UltraHD televisions

BENEFITS

Clean Installations: Slimline cables offer a slim form factor for flexibility and better cable management

Maximum Quality: Premium HDMI cables ensure the best quality for feature-rich 4K UltraHD devices

HDMI SELECTION CHART

	Premium HDMI		HDMI	
	Slim Line	In-Wall	In-Wall	
	AC3MP1-WH AC3MP2-WH	AC2MP1-BK AC2MP2-BK AC2MP3-BK AC2MP4-BK AC2AP5-BK AC2AP7-BK	AC2M00-BK AC2M01-BK AC2M02-BK AC2M03-BK AC2M04-BK	AC2M05-BK AC2M07-BK AC2M10-BK AC2M15-BK AC2M20-BK
Third Party Tested	•	•		
In-Wall Rated		CL3	CMG/CL3/FT4	
Bandwidth	18.6 Gbps	18.6 Gbps	10.2 Gbps	
4K Resolution at 30 fps	•	•	•	
4K Resolution at 60 fps	•	•	Requires electronics support of signal compression	
High Dynamic Range (HDR)	•	•		
Rec. 2020 color space	•	•		
YCbCr 4:2:0	•	•		
32 channel audio	•	•		
1536 kHz total audio	•	•		
4 audio streams	•	•		
2 video streams (Dual View)	•	•		
21:9 aspect ratio	•	•		
Audio return channel (ARC)	•	•	•	
3D support	•	•	•	
Ethernet channel	•	•	•	



designed to be better™



Legrand, North America

60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca