

---

## CATEGORY 5 BLACK AND WHITE BULLET CAMERA KIT

CM7645 | [On-Q](#)



---

### FEATURES & BENEFITS

This black and white camera kit features the same capabilities as the color camera kit, but in a more affordable package. Based on Cat 5 cabling, installation is cost effective and simple. Included cameras are weatherproof and good for indoor or outdoor applications.

**Kit Includes:**

- 1 **CM1011 CAT5 Camera Module**
- 2 **F2284 Black and White Bullet Cameras**
- 1 **F1001 Modulator with power supply**
- 1 **CM1017 RCA Patch Cable**
- 1 **PW7725 Power Supply**

Requires part number **F7642** for audio use.

---

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: RCA Patch Cable: RG Shielded Coaxial Cable

Color: Modulator: Black

Cameras: White

Camera Module: Gray

Connection Type: Patch Cable: RCA, Gold Plated

Type: Camera/Modulator Kit

Input Plug Type: Camera Module: 4 x RJ45 Input Jacks

Modulator: F Connector

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 45111801

#### DIMENSIONS

Depth (US): Modulator: 4.75

Height (US): Modulator: 1.625"

Width (US): Modulator: 3.625 in

## **CORD INFORMATION**

Connector Type End One: Patch Cable: 1 x RCA Plug  
Connector Type End Two: Patch Cable: 1 x RCA Plug  
Cord Length US: Patch Cable: 12.0"

## **TECHNICAL INFORMATION**

AC Voltage Input: Modulator: 110 V Power Supply included  
Amps: 800 mA  
Compatible Power Supplies: LCD Module: PW7725 (included)  
Frequency: UHF: Channels 14 to 69  
Cable: Channels 60 to 94 and 100 to 125  
Frequency Response: Modulator: +/-3 dB max from 100 Hz to 10K Hz with 1K Hz as a reference  
Jack Connectors: RJ45 and RCA  
Material: Faceplate: Plastic ABS  
OhmValue: Patch Cable: 75 Ohm  
Modulator: 10K Ohm min input impedance from 1K Hz to 10K Hz  
Operating Temperature (Celsius): -10°C to 50°C  
Output And Line Out Connection: Camera Module: 4 x RCA Audio Out, 4 x RCA Video Out, 1 RCA Video Sequence Out  
Volts (DC): Camera Module: 12 VDC  
Watts: Camera Module: 9.6 W max