



## DIGITAL AUDIO TWO-ROOM, MULTI-SOURCE KIT, WHITE

AU7252-WH | [On-Q](#)

### FEATURES & BENEFITS

The AU7252-WH is a two-room, multi-source Digital Audio Kit. Conveniently supplying all of the core components necessary to install a two-room Digital Audio System with digital and analog source accessibility, this kit comes complete with (2) AU7010-WH Digital Audio Amplified Keypads, (1) AU7000 Digital Audio Distribution Module, (1) AU7001 Digital Audio Input Module, (1) AU7007-WH Digital Audio Global Source Input, (1) PW1020 Digital Audio Power Distribution Module, (1) PW1060 Power Supply, and (1) PW7760 Power Supply.

Check out the [Digital Audio mobile app](#).



- Comes complete with all core components for a two-room, multi-source Digital Audio System with digital and analog source accessibility
- Built-in access to streaming services including, Spotify, iHeartRadio, Pandora, Napster, SiriusXM, and TuneIn
- Allows streaming of networked digital content from iTunes, Windows Media Player libraries, and mobile devices
- Offers global access to analog source equipment
- Provides 20 watts of Class D power per zone
- Conveniently controllable through both included keypads as well as free, intuitive Android or iOS apps for smartphones and tablets
- Provides all core components needed to install a two-room, multi-source Digital Audio System with digital and analog source accessibility
- Structured wiring based to offer easy installation and a repeatable solution
- Simple setup using smartphone or tablet, no PC required

\*Streaming services subject to geographic availability. Service subscriptions may be required.

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: Connect Cat5e or better and speaker wire 18-16 gauge.  
Color: White  
Size: 8.25" x 8.25" x 13.5"  
Termination: 918.84 cu. in.  
Connection Type: RJ45 connections and removeable pheonix screw down terminals  
Type: Low Voltage, Audio System  
Special Features: 2-Zone, 4-Source Digital Audio System  
Style: Decorator Keypad; Structured wiring cabinet (not included)

#### **LISTING AGENCIES/THIRD PARTY CERTIFICATIONS**

RoHS: Yes  
FCC Standard: Yes  
UL Standard: Yes

#### **DIMENSIONS**

Depth (Metric): 342.9mm  
Depth (US): 13.5"  
Width (Metric): 209.55mm  
Width (US): 8.25"  
Primary Packaging Weight (Metric): 2.5 kg  
Product Weight (Metric): 2.5 kg  
Product Weight (US): 5.5 lbs  
Volume: 918.84 cu. in.  
Weight: 5.5 lbs  
Height: 8.25"

#### **TECHNICAL INFORMATION**

Connection Method: Ethernet network  
Mounting: Wall Mount/Enclosure Mount  
Power Requirements: 24 VDC 60W Power Supply / 12 VDC 18W Power Supply  
Supported Standards: FCC, UL, RoHS  
Watts: 20W 8Ω  
Connection Location: Data Control Interface: Ethernet/Digital Keypad

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA