



LYRIQ LOCAL SOURCE INPUT, IVORY

F7417-IV | [On-Q](#)

FEATURES & BENEFITS

Allows user to plug in devices like portable audio players, master bedroom TVs, or computer audio outputs for in-room listening on local speakers. Automatically overrides the remote source music in the room when the local source is on and returns to source when local source is off.

- Automatically overrides the remote source
- For use with the lyriQ Audio System

SPECIFICATIONS

GENERAL INFO

Cable Type: Cat5e
Color: Ivory
Product Series: Classic
Type: Audio Source Input
Input Plug Type: RCA Male

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Screws

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 45111801

CONSTRUCTION INFORMATION

Installation Location: In-Wall

DIMENSIONS

Height (Metric): 10.7 cm
Height (US): 4.2"
Width (Metric): 4.2 cm
Width (US): 1.65 in

CORD INFORMATION

Connector Type End One: Gold-plated RCA Jack

Connector Type End Two: RJ45 Female

Pinning:

1. Green/White L- (PreGND)
2. Green L+
3. Orange/White (PreGND) Audio R-
4. Blue IR_IN (IR TX)
5. Blue/White Status_Out (IR RX)
6. Orange Audio R+
7. Brown/White Ground
8. Brown Power (+24 Vdc)

TECHNICAL INFORMATION

Material: ABS

Mounting: Wall

Receptacle Type: RCA Female

Number Of Receptacles: 2