



Actual

Catalog Number: RC55PT
Product ID: 7TAI029860R0060
UPC Number: 78621003420
EAN Number: 05414363159391
Status: Active

Vinyl Insulated Pin Terminal, Length 1.04 Inches, Pin Length .390 Inches, Diameter .106 Inches, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated, 500 Pack

- Provides an easy and effective way to terminate stranded wire into European/metric-style terminal blocks.
- Application Tools: ERG4001
- Alternate Package Qty: 10RC-55PT

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Pin Terminal
Special Features	Provides an easy and effective way to terminate stranded wire into European/metric-style terminal blocks.
Standard	UL E9809
Wire Size	12-10
Voltage Rating	300V
Material	Copper
Color	Yellow

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Pin shape
Insulation	PVC
Colour insulation	Yellow
Reel packaging	N
AWG-range	12-10
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	500
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	5000
Outer Dimensions (inches)	24x10.7x7
Weight Uom	8.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com