



## TOUCH™ WI-FI READY MASTER DIMMER, INCANDESCENT / HALOGEN, MAGNESIUM

ADTH600RMHM1 | [adorne](#)

### FEATURES & BENEFITS

#### USAGE

- Perfect anywhere you'd like to combine Wi-Fi-Ready lighting control with sleek, recognizable touch technology and the option to dim.
- The Touch Wi-Fi Ready Master Dimmer is a programmable light switch and dimmer combination that pairs with the adorne Hub to create smart lighting solutions for your home.
- Turn lights on and off or dim with just the touch of a finger – or create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app.
- This item is also available in [white](#).

#### GETTING STARTED

- Time to install: 25 minutes or less.
- Easily install this Master dimmer into an existing electrical box and wire directly to the light.
- Once the Master dimmer is installed, a Touch Wi-Fi Ready Remote Dimmer may be installed to allow for Wi-Fi Ready control of a light from two locations without rewiring. Simply follow the instructions after installing to pair with the Master dimmer.
- Innovative snap-in system ensures easy installation.
- The Legrand Lighting Control app is available for free on iTunes and Google Play.
- This item requires the [adorne Hub](#). Shop now to learn how Wi-Fi lighting solutions can transform your home.
- This item requires an adorne Wall Plate. [Shop now](#) to choose from dozens of finishes including a variety of luxurious metals, or order in your own custom finish.
- Looking to integrate other party advanced automation systems? Visit our [partners page](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Magnesium  
Product Series: adorne Touch  
Type: 2-wire  
Style: Touch

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes  
FCC Standard: Yes  
UL Listing No: UL 1472  
UL Standard: Yes

UN SPSC: 39122206

## DIMENSIONS

Depth (US): 1.79"

Height (US): 4.185"

Length (US): 4.20"

Width (US): 1.77"

Product Weight (US): 0.32 pounds

## TECHNICAL INFORMATION

AC Voltage Output: 120VAC

Frequency: 900 MHz (RF)

Humidity: 0-80% relative humidity, noncondensing

Load: Incandescent, Halogen

Material: FR4(PCB)

Mounting: USA Electrical Wiring Box / adorne Mounting Plate

Operating Temperature (Celsius): 0°C to 50°C

Product Fits Into: Wall

Storage Temperature: 32°F to 122°F

Watts: 600W Load Dependent