



## TOUCH™ WI-FI READY REMOTE DIMMER, WHITE

ADTHRRW1 | [adorne](#)

### FEATURES & BENEFITS

#### USAGE

- Perfect anywhere you'd like to combine Wi-Fi-Ready lighting control with sleek, recognizable touch technology and the option to dim.
- The Touch Wi-Fi Ready Remote Dimmer is a programmable light switch and dimmer combination that pairs with the adorne Hub and the Touch Wi-Fi Ready Master Dimmer to create smart lighting solutions for your home.
- Turn lights on and off or dim with the touch of a finger – or create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app.
- This item is also available in [magnesium](#).

\*HGTV, HGTV Smart Home, HGTV Smart Home Giveaway and their associated logos are trademarks of Scripps Network, LLC. Used with permission, all rights reserved.

#### GETTING STARTED

- Time to install: 25 minutes or less.
- The Touch Wi-Fi Ready Remote Dimmer lets you control a light from a new location without running new wires. Simply install and pair with a Touch Wi-Fi Ready Master Dimmer via the easy-to-follow instructions.
- This item is meant to be paired with the Touch Wi-Fi Ready Master Dimmer, which installs directly to the light. Together they allow for customizable control of a single lighting source from two locations or from your smartphone.
- The Legrand Lighting Control app is available for free on iTunes and Google Play.
- This item requires the [adorne Hub](#). Shop now to learn how Wi-Fi lighting solutions can transform your home.
- This item requires an adorne Wall Plate. [Shop now](#) to choose from dozens of finishes including a variety of luxurious metals, or order in your own custom finish.
- Looking to integrate other party advanced automation systems? Visit our [partners page](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Product Series: adorne Touch  
Style: Touch

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes  
FCC Standard: Yes

UL Listing No: UL 1472  
UL Standard: Yes  
UN SPSC: 39112401

#### **DIMENSIONS**

Depth (US): 1.79"  
Height (US): 4.185"  
Length (US): 4.20"  
Width (US): 1.77"  
Product Weight (US): 0.25 pounds

#### **TECHNICAL INFORMATION**

AC Voltage Output: 120VAC  
Frequency: 900 MHz (RF)  
Humidity: 0-80% relative humidity, noncondensing  
Material: FR4(PCB)  
Mounting: USA Electrical Wiring Box / adorne Mounting Plate  
Operating Temperature (Celsius): 0°C to 50°C  
Storage Temperature: 32°F to 122°F  
Watts: Auxiliary Remote Dimmer - No Load