



## SOFTAP™ WI-FI READY REMOTE DIMMER, MAGNESIUM

ADTPRRM1 | [adorne](#)

### FEATURES & BENEFITS

#### USAGE

- Perfect anywhere you'd like to combine Wi-Fi lighting control with sensitive softTap technology and the option to dim.
- The softTap Wi-Fi Ready Remote Dimmer is a programmable light switch and dimmer combination that pairs with the adorne Hub and the softTap Wi-Fi Ready Master Dimmer to create smart lighting solutions for your home.
- Turn lights on and off or dim with just the light tap of a finger – or create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app.
- This item is also available in [white](#).

\*HGTV, HGTV Smart Home, HGTV Smart Home Giveaway and their associated logos are trademarks of Scripps Network, LLC. Used with permission, all rights reserved.

#### GETTING STARTED

- Time to install: 25 minutes or less.
- The softTap Wi-Fi Ready Remote Dimmer lets you control a light from a new location without running new wires. Simply install and pair with a softTap Wi-Fi Ready Master Dimmer via the easy-to-follow instructions.
- This item is meant to be paired with the [softTap Wi-Fi Ready Master Dimmer](#), which installs directly to the light. Together they allow for customizable control of a single lighting source from two locations or from your smartphone.
- This item uses patented Tru-Universal technology, enabling the dimmer to support all load types including incandescent/halogen, magnetic low voltage (MLV), electronic low voltage (ELV) in forward or reverse phase, CFL/LED, etc.
- The Legrand Lighting Control app is available for free on iTunes and Google Play.
- This item requires the adorne Hub. [Shop now](#) to learn how Wi-Fi ready lighting solutions can transform your home.
- This item requires an adorne Wall Plate. [Shop now](#) to choose from dozens of finishes including a variety of luxurious metals, or order in your own custom finish.
- Looking to integrate other party advanced automation systems? Visit our [partners page](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Magnesium  
Product Series: adorne softTap  
Style: SofTap

## LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes  
FCC Standard: Yes  
UL Listing No: UL 1472  
UL Standard: Yes  
UN SPSC: 39112401

## DIMENSIONS

Depth (US): 1.79"  
Height (US): 4.185"  
Length (US): 4.20"  
Width (US): 1.77"  
Product Weight (US): 0.25 pounds

## TECHNICAL INFORMATION

AC Voltage Output: 120VAC  
Frequency: 900 MHz (RF)  
Humidity: 0-80% relative humidity, noncondensing  
Material: FR4(PCB)  
Mounting: USA Electrical Wiring Box / adorne Mounting Plate  
Operating Temperature (Celsius): 0°C to 50°C  
Product Fits Into: Wall  
Storage Temperature: 32°F to 122°F  
Watts: Auxiliary Remote Dimmer - No Load