



## SOFTAP™ WI-FI READY MASTER SWITCH, MAGNESIUM

ASTP155RMM1 | [adorne](#)

---

### FEATURES & BENEFITS

#### USAGE

- Perfect anywhere you'd like to combine custom Wi-Fi lighting control with sensitive softTap technology.
- The softTap Wi-Fi Ready Master Switch is a programmable light switch that pairs with the adorne Hub to create smart lighting solutions for your home.
- Turn lights on and off with just the light tap of a finger – or create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app.
- This item is also available in [white](#).

\*HGTV, HGTV Smart Home, HGTV Smart Home Giveaway and their associated logos are trademarks of Scripps Network, LLC. Used with permission, all rights reserved.

#### GETTING STARTED

- Time to install: 25 minutes or less.
- Easily install this Master switch into an existing electrical box and wire directly to the light.
- Once the master switch is installed, a [softTap Wi-Fi Ready Remote Switch](#) may be installed to allow for Wi-Fi control of a light from two locations without rewiring. Simply follow the instructions after installing to pair with the Master switch.
- Innovative snap-in system ensures easy installation.
- The Legrand Lighting Control app is available for free on iTunes and Google Play.
- This item requires the [adorne Hub](#). [Shop now](#) to learn how Wi-Fi lighting solutions can transform your home.
- This item requires an adorne Wall Plate. [Shop now](#) to choose from dozens of finishes including a variety of luxurious metals, or order in your own custom finish.
- Looking to integrate other party advanced automation systems? Visit our [partners page](#).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Magnesium  
Product Series: adorne softTap  
Style: SofTap

## LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes  
FCC Standard: Yes  
UL Listing No: UL 508  
UL Standard: Yes  
UN SPSC: 39121107

## DIMENSIONS

Depth (US): 1.63"  
Height (US): 4.185"  
Length (US): 2.66"  
Width (US): 1.77"  
Product Weight (US): 0.25 pounds

## TECHNICAL INFORMATION

AC Voltage Output: 120VAC  
Frequency: 900 MHz (RF)  
Humidity: 0-80% relative humidity, noncondensing  
Load: Incandescent, Halogen, ELV, MLV, Fluorescent  
Material: FR4(PCB)  
Mounting: USA Electrical Wiring Box / adorne Mounting Plate  
Operating Temperature (Celsius): 0°C to 50°C  
Product Fits Into: Wall  
Storage Temperature: 32°F to 122°F  
Watts: 1800 W