



SOFTAP™ WI-FI READY REMOTE SWITCH, WHITE

ASTPRRW1 | [adorne](#)

FEATURES & BENEFITS

USAGE

- Perfect anywhere you'd like to combine custom Wi-Fi lighting control with sensitive softTap technology.
- The softTap Wi-Fi Ready Remote Switch is a programmable light switch that pairs with the adorne Hub and the softTap Wi-Fi Ready Master Switch to create smart lighting solutions for your home.
- Turn lights on and off with just the light tap of a finger – or set custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app.
- This item is also available in [magnesium](#).

GETTING STARTED

- Time to install: 25 minutes or less.
- The softTap Wi-Fi Ready Remote Switch lets you control a light from a new location without running new wires. Simply install and pair with the [softTap Wi-Fi Ready Master Switch](#) via the easy-to-follow instructions and enjoy customizable control of a single lighting source from two locations or your smartphone.
- The Legrand Lighting Control app is available for free on iTunes and Google Play.
- This item requires the adorne Hub. [Shop now](#) to learn how Wi-Fi ready lighting solutions can transform your home.
- This item requires an adorne Wall Plate. [Shop now](#) to choose from dozens of finishes including a variety of luxurious metals, or order in your own custom finish.
- Looking to integrate other party advanced automation systems? Visit our [partners page](#).

SPECIFICATIONS

GENERAL INFO

Color: White
Product Series: adorne softTap
Style: SoftTap

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes
FCC Standard: Yes
UL Listing No: UL 508
UL Standard: Yes

UN SPSC: 39121107

DIMENSIONS

Depth (US): 1.63"

Height (US): 4.185"

Length (US): 2.66"

Width (US): 1.77"

Product Weight (US): 0.18 pounds

TECHNICAL INFORMATION

AC Voltage Output: 120VAC

Frequency: 900 MHz (RF)

Humidity: 0-80% relative humidity, noncondensing

Load: All

Material: FR4(PCB)

Mounting: USA Electrical Wiring Box / adorne Mounting Plate

Operating Temperature (Celsius): 0°C to 50°C

Storage Temperature: 32°F to 122°F

Watts: Auxiliary Remote Switch - No Load