



TRACJACK PLASTIC SURFACE MOUNT BOX FOR UP TO FOUR MODULES OUT SINGLE SIDE, FOG WHITE

OR-404TJ4 | [Ortronics](#)

FEATURES & BENEFITS

Ortronics TracJack Surface Mount Outlet Boxes accept front-loading TracJack modules and provide snap-on covers and snap-in label fields. Boxes are supplied with screws and double-sided adhesive tape for mounting onto almost any surface



- Low profile compact design
- Base plate and snap-on cover design
- Front-load module approach
- Textured finish
- Holds four TracJack modules
- Recessed label fields
- Compatible with LabelMO XL
- Designed to seamlessly intergrate with Wiremold 2700, 2800 and 2900 raceways.

SPECIFICATIONS

GENERAL INFO

Color: Fog White
Footprint: TracJack
Number Of Ports: 4
Product Series: Clarity
Type: Plates and Boxes

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-20*19 mm (Pan Head) 2ea | #6-32*25 mm Screw (Binding Head) 2ea

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CUL Listing No: E131600

UL Listing No: E131600

UL Standard: Yes

CONSTRUCTION INFORMATION

Component 1: Plastic TracJack Surface Box

Material 1: High Impact Thermoplastic ABS 94V-0

DIMENSIONS

Depth (Metric): 29.46 mm

Height (Metric): 90.67 mm

Height (US): 3.57"

Width (Metric): 119.38 mm

TECHNICAL INFORMATION

Capacity: Up to four TracJack modules

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant