



TRACJACK FACEPLATE, TWO-PORT (SINGLE GANG), PLASTIC, FOG WHITE

OR-40300548 | [Ortronics](#)

FEATURES & BENEFITS

Ortronics Single Gang Plastic Faceplates accept front-loading TracJack modules and include two snap-in label fields



- **Low profile design:** Blends with most environments.
- **Recessed label fields:** Supports TIA/EIA 606 standard.
- **Easily accepts snap-in TracJacks:** Easily field configured.
- **Front-load module approach:** Improves access for future work.
- **Textured finish:** Hides future scuffs.
- **Oval mounting holes:** Assists proper alignment

SPECIFICATIONS

GENERAL INFO

Color: Fog White
Footprint: TracJack
Number Of Ports: 2
Product Series: Clarity
Type: Plates and Boxes

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-32*25 mm Screw, Binding Head (2 ea)

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

CONSTRUCTION INFORMATION

Component 1: Plastic TracJack Faceplate

Material 1: High Impact Thermoplastic 94V-0 ABS/PC/BLEND

DIMENSIONS

Depth (Metric): 7.62 mm

Height (Metric): 114.3 mm

Height (US): 4.5"

Width (Metric): 69.85 mm

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant