



TRACJACK STYLISTICS FRAME, FOUR-PORT, CLOUD WHITE

OR-41900018-88 | [Ortronics](#)

FEATURES & BENEFITS

TracJack Stylistics Plastic Duplex Frame accepts four front-loading TracJack modules in the rectangular electrical mounting footprint of a GFCI outlet. It is compatible with many cable delivery systems that can house electrical duplex outlets



- **Matches rectangular electrical outlet (GFI) footprint:** Supports use with electrical delivery system.
- **Field configurable with TracJacks:** Design or site flexibility for new or retrofit.
- **Supports TracJack footprint:** Broad offering of connector options.
- **Front load and access:** Connector access without removing plate.
- **Choice of colors:** Compatible with many environments.

SPECIFICATIONS

GENERAL INFO

Color: Cloud White
Footprint: TracJack
Number Of Ports: 4
Product Series: Clarity
Type: Plates and Boxes

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-32*25 mm Screw, Binding Head (2 ea)

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

CONSTRUCTION INFORMATION

Component 1: Plastic TracJack Mounting Frame
Material 1: High Impact Thermoplastic ABS 94V-0

DIMENSIONS

Depth (Metric): 11.43 mm
Height (Metric): 103.88 mm
Height (US): 4.09"
Width (Metric): 44.45 mm

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: TAIWAN
Buy American Act Status: Trade Agreement Act Compliant