

Date: \_\_\_\_\_  
 In hands date of project: \_\_\_\_\_  
 Project name/Number: \_\_\_\_\_  
 Name of distributor: \_\_\_\_\_  
 Client #: \_\_\_\_\_  
 Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

Order code: 64668  
 Description: LED/T8/S3/18W/840/48/STD  
 UPC: 69549646681  
 Case quantity: 25



Nominal length : 48 in. (1 220 mm) Dia. : 1 in. (26 mm)

### PERFORMANCE DATA

Shape: T8  
 Base: G13  
 Starting method: Instant, Rapid & Program Start  
 Lamp voltage (VAC): 120 V-277 V/347 V  
 Color temperature (K)\*\*: 4 000  
 Average life (L70 hours): 50 000  
 CRI: 83  
 Beam angle (°): 240  
 Operating temperature range: -20°C / -4°F to 45°C / 113°F

\*Initial lumens range: +/- 10 %

\*\*Typical colour temperature range: +/- 5 %

Order code	Average System Watts (W)			Initial Lumens (lm)*		
	LBF	NBF	HBf	LBF	NBF	HBf
64668	17	22	30	1 750	2 300	3 050



DAMP



COMPLIANT



NO  
MERCURY



WARRANTY



### CAUTIONS

THIS LAMP OPERATES ON INSTANT START, RAPID START AND MANY PROGRAM START ELECTRONIC BALLASTS.  
 Direct replacement for 32 watts lamps only. Risk of fire. Do not install this lamp in a pre-heat luminaire. Risk of electric shock – for use in damp locations.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_

Date: \_\_\_\_\_

Data is based upon tests performed in a controlled environment and representative of relative performance.  
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

October 17, 2017

**STANDARD®**