

---

## TRACJACK PLASTIC SURFACE MOUNT BOX FOR UP TO FOUR MODULES OUT SINGLE SIDE, CLOUD WHITE

OR-404TJ4-88 | [Ortronics](#)



---

### FEATURES & BENEFITS

Ortronics TracJack Surface Mount Outlet Boxes accept front-loading TracJack modules and provide snap-on covers and snap-in label fields. Boxes are supplied with screws and double-sided adhesive tape for mounting onto almost any surface. Compatible with Wiremold 2700, 2800 and 2900 raceway series.



- Low profile compact design
- Base plate and snap-on cover design
- Front-load module approach
- Textured finish
- Holds four TracJack modules
- Recessed label fields
- Compatible with LabelMO XL
- Designed to seamlessly intergrate with Wiremold 2700, 2800 and 2900 raceways.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Cloud White  
Footprint: TracJack  
Number Of Ports: 4  
Product Series: Clarity  
Type: Plates and Boxes

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-20\*19 mm (Pan Head) 2ea | #6-32\*25 mm Screw (Binding Head) 2ea

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CUL Listing No: E131600

UL Listing No: E131600

UL Standard: Yes

#### **CONSTRUCTION INFORMATION**

Component 1: Plastic TracJack Surface Box

Material 1: High Impact Thermoplastic ABS 94V-0

#### **DIMENSIONS**

Depth (Metric): 29.46 mm

Height (Metric): 90.67 mm

Height (US): 3.57"

Width (Metric): 119.38 mm

#### **TECHNICAL INFORMATION**

Capacity: Up to four TracJack modules

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant