



TRACJACK USOC SIX-POSITION RJ25C, ELECTRICAL IVORY

OR-6370005-13 | [Ortronics](#)

FEATURES & BENEFITS

TracJack Module provides a single RJ25C six-position jack. TracJack is a versatile single jack solution in a front-load footprint which allows a choice of up to six jacks/connectors to fit in a single gang plate



- Front removable
- Traditional 110 termination
- Standard TracJack footprint
- Icon compatible, with Category 5e marking on jack face

SPECIFICATIONS

GENERAL INFO

Color: Electrical Ivory
Footprint: TracJack
Number Of Ports: 1
Product Series: Clarity
Type: Jacks and Modules

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E131600
UL Listing No: E131600

CONSTRUCTION INFORMATION

Component 1: Plastic TracJack Housing
Component 2: Array of six linear modular contacts
Component 3: IDC contacts, 110 D2
Component 4: Printed circuit board

Finish Plating 2: Nickel plating and a minimum of 50 micro inches of selective gold plating in contact area

Finish Plating 3: Nickel plating and tin lead over plate

Material 1: High Impact Thermoplastic ABS 94V-0

Material 2: Phosphor bronze

Material 3: Phosphor bronze

Material 4: Two-sided FR-4 epoxy resin/glass base with solder mask

DIMENSIONS

Depth (Metric): 34.04 mm

Height (Metric): 23.37 mm

Height (US): 0.92"

Width (Metric): 18.54 mm

TECHNICAL INFORMATION

Performance Rating: USOC six-position

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

