



## TRACJACK FACEPLATE, ONE-PORT (SINGLE GANG), PLASTIC, CLOUD WHITE

OR-40300549-88 | [Ortronics](#)

### FEATURES & BENEFITS

Ortronics Single Gang Plastic Faceplates accept front-loading TracJack modules and include two snap-in label fields



- **Low profile design:** Blends with most environments.
- **Recessed label fields:** Supports TIA/EIA 606 standard.
- **Easily accepts snap-in TracJacks:** Easily field configured.
- **Front-load module approach:** Improves access for future work.
- **Textured finish:** Hides future scuffs.
- **Oval mounting holes:** Assists proper alignment

### SPECIFICATIONS

#### GENERAL INFO

Color: Cloud White  
Footprint: TracJack  
Number Of Ports: 1  
Product Series: Clarity  
Type: Plates and Boxes

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-32\*25 mm Screw, Binding Head (2 ea)

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CUL Listing No: E131600  
UL Listing No: E131600  
UL Standard: Yes

#### CONSTRUCTION INFORMATION

Component 1: Plastic TracJack Faceplate

Material 1: High Impact Thermoplastic 94V-0 ABS/PC/BLEND

**DIMENSIONS**

Depth (Metric): 7.62 mm

Height (Metric): 114.3 mm

Height (US): 4.5"

Width (Metric): 69.85 mm

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant