



## TRACJACK FACEPLATE, SIX-PORT (DUAL GANG), PLASTIC, WIREMOLD IVORY

OR-40300555-99 | [Ortronics](#)

### FEATURES & BENEFITS

Ortronics Double Gang Plastic Faceplates accept front-loading TracJack modules and include four snap-in label fields



- **Low profile design:** Blends with most environments.
- **Recessed label fields:** Supports TIA/EIA 606 standard.
- **Easily accepts snap-in TracJacks:** Easily field configured.
- **Front-load module approach:** Improves access for future work.
- **Textured finish:** Hides future scuffs.
- **Oval mounting holes:** Assists proper alignment

### SPECIFICATIONS

#### GENERAL INFO

Color: Wiremold Ivory  
Footprint: TracJack  
Number Of Ports: 12  
Product Series: Clarity  
Type: Plates and Boxes

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: #6-32\*25 mm Screw, Binding Head (4 ea)

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CUL Listing No: E131600  
UL Listing No: E131600  
UL Standard: Yes

## CONSTRUCTION INFORMATION

Component 1: Plastic TracJack Faceplate

Material 1: High Impact Thermoplastic 94V-0 ABS/PC/BLEND

## DIMENSIONS

Depth (Metric): 7.62 mm

Height (Metric): 114.3 mm

Height (US): 4.5"

Width (Metric): 114.3 mm

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MALAYSIA

Buy American Act Status: Exception

Note: Contact Customer Support for Buy American Act options