

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020211](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway Rubber Hand Lamp with Switch & Receptacle

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130102](#)
 NEMA Configuration N/A
 Outlet Side
 Overview [Hand Lamps](#)
 Product Name Super-Safeway
 Type Hand Lamps
 UPC 78678860896
 Woodhead Yes

Physical

Cord Length - Primary 7.62m (25.0')
 Cord Length - Secondary N/A
 Depth 80.01mm (3.150")
 Duty Industrial
 Guard Included No
 Guard Type N/A
 Height 174.63mm (6.875")
 Length N/A
 Material - Guard N/A
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Incandescent
 Cord Type - Primary 16/3 SOOW
 Lamp Type A21
 Lamp Wattage - Maximum 100W
 Lumens 1000
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 240V

Material Info

Engineering Number 1175US



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

China RoHS

Search Parts in this Series

[130102 Series](#)