

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020247](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Safeway Phenolic Hand Lamp with Switch and Outlet

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family	Portable Lighting
Series	130102
NEMA Configuration	N/A
Outlet	Side
Overview	Hand Lamps
Product Name	Safety Yellow
Type	Hand Lamps
UPC	78678860925
Woodhead	Yes
Physical	
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	6.045mm (2.380")
Duty	Commercial
Guard Included	No
Guard Type	N/A
Height	165.10mm (6.500")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V
Material Info	
Engineering Number	270-3



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130102 Series](#)