

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301530030](#)  
**Status:** **Active**  
**Overview:** Ground Fault Circuit Interrupter (GFCI) Products  
**Description:** Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, Molded NEMA 5-15 Tri-Tap, 15A, 120V, 0.61m (2.0') Cord Length

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E66308

**General**

Product Family Power Distribution  
 Series [130153](#)  
 Enclosure Rating NEMA 3R  
 GFCI Reset Manual  
 Mounting Style Portable  
 Open Neutral Relay Yes  
 Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)  
 Product Literature Order No 987650-7737  
 Product Name Super-Safeway  
 Receptacle Type N/A  
 Type GFCI Industrial Duty, Single Phase  
 UPC 78678889750  
 Woodhead Yes

**Physical**

Cord Diameter 10.92mm (.430")  
 Cord Grip Body Size Internal Double C-Clamp  
 Cord Length 0.61m (2.0')  
 Feed-Thru Yes  
 Flip Lid No  
 Material - Housing Nylon  
 Number of Receptacles 3  
 Packaging Type Bag

**Electrical**

Cord Type 12/3 SJTW  
 Current - Maximum per Contact 15.0A  
 GFCI Yes-In-line  
 Ground Continuity Monitor No  
 NEMA Configuration NEMA 5-15  
 Voltage - Maximum 120V

**Material Info**

Engineering Number 15050-3TTM

**Reference - Drawing Numbers**

Sales Drawing SD-130153-014



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130153 Series](#)